

Eaton JBXFC1G02FCNDSR

Right angle plug, IP40, size 1, 2 female contacts, cable clamp backshell;
JBXFC1G02FCNDSR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXFC1G02FCNDSR
PRODUCT LENGTH/DEPTH	36.5 mm
PRODUCT HEIGHT	33.5 mm
PRODUCT WIDTH	12 mm
PRODUCT WEIGHT	20.73 g
COMPLIANCES	UL 1977

CURRENT RATING	15 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
TEST CURRENT	15 A UL
TEST VOLTAGE	760 V UL
BACKSHELL ANGLE	90°
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	2
PLATING	Black Anodized
PLUG TYPE	Right Angle Plug
SHELL MATERIAL	Brass
SHELL SIZE	1
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	2
SALT SPRAY	96 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

