

Eaton JBXFC2G02FCSDSR

Right angle plug, IP40, size 2, 2 female contacts, cable clamp backshell;
JBXFC2G02FCSDSR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXFC2G02FCSDSR
PRODUCT LENGTH/DEPTH	42.5 mm
PRODUCT HEIGHT	36.5 mm
PRODUCT WIDTH	15 mm
PRODUCT WEIGHT	33.67 g
COMPLIANCES	UL 1977

CURRENT RATING	30 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	REACH RoHS
TEST CURRENT	30 A UL
TEST VOLTAGE	1000 V UL
BACKSHELL ANGLE	90°
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	2
PLATING	Nickel Chrome
PLUG TYPE	Right Angle Plug
SHELL MATERIAL	Brass
SHELL SIZE	2
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	2
SALT SPRAY	48 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: