



# Eaton

## JBXFC2G08FCNDSMR

Right angle plug, IP40, size 2, 8 female contacts, cable clamp protective boot; JBXFC2G08FCNDSMR

□□□□

|                                 |                                                                          |
|---------------------------------|--------------------------------------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Souriau JBX series<br>IP40 / IP68 metallic push-<br>pull connector |
| <b>CATALOG NUMBER</b>           | JBXFC2G08FCNDSMR                                                         |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 42.5 mm                                                                  |
| <b>PRODUCT HEIGHT</b>           | 36.5 mm                                                                  |
| <b>PRODUCT WIDTH</b>            | 15 mm                                                                    |
| <b>PRODUCT WEIGHT</b>           | 34.12 g                                                                  |
| <b>COMPLIANCES</b>              | UL 1977                                                                  |

Product specifications

|                 |                                     |
|-----------------|-------------------------------------|
| BACKSHELL ANGLE | 90°                                 |
| BACKSHELL TYPE  | Sealing Gland With<br>Optional Boot |

□□

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□  
Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2025 □□ □□□□□□□□

Follow us on social media to get the latest product and support information.

