

Eaton

JBXFC3G08FCNDSMR

Right angle plug, IP40, size 3, 8 female contacts, cable clamp protective boot; JBXFC3G08FCNDSMR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXFC3G08FCNDSMR
PRODUCT LENGTH/DEPTH	50.5 mm
PRODUCT HEIGHT	45 mm
PRODUCT WIDTH	18 mm
PRODUCT WEIGHT	60.54 g
COMPLIANCES	UL 1977

CURRENT RATING	12 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
TEST CURRENT	12 A UL
TEST VOLTAGE	830 V UL
BACKSHELL ANGLE	90°
BACKSHELL TYPE	Sealing Gland With Optional Boot
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
PLATING	Black Anodized
PLUG TYPE	Right Angle Plug
SHELL MATERIAL	Brass
SHELL SIZE	3
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	8
SALT SPRAY	96 hour

PROJECT NAME:	
PROJECT NUMBER:	
PREPARED BY:	
:	