

# Eaton

## JBXFC3G18FCSDSMR

Right angle plug, IP40, size 3, 18 female contacts, cable clamp protective boot; JBXFC3G18FCSDSMR

<b>PRODUCT NAME</b>	Eaton Souriau JBX series IP40 / IP68 metallic push-pull connector
<b>CATALOG NUMBER</b>	JBXFC3G18FCSDSMR
<b>PRODUCT LENGTH/DEPTH</b>	50.5 mm
<b>PRODUCT HEIGHT</b>	45 mm
<b>PRODUCT WIDTH</b>	18 mm
<b>PRODUCT WEIGHT</b>	61.36 g
<b>COMPLIANCES</b>	UL 1977



Powering Business Worldwide

<b>CURRENT RATING</b>	7 A UL
<b>FITTED WITH:</b>	Shielding
<b>ENVIRONMENTAL CONDITIONS</b>	RoHS REACH
<b>TEST CURRENT</b>	7 A UL
<b>TEST VOLTAGE</b>	660 V UL
<b>BACKSHELL ANGLE</b>	90°
<b>BACKSHELL TYPE</b>	Sealing Gland With Optional Boot
<b>CONNECTOR ACCESSORY OPTION</b>	Delivered with connector
<b>CONNECTOR TYPE</b>	Plug
<b>CONTACT DELIVERY</b>	Unloaded
<b>CONTACT GENDER</b>	Socket (Female)
<b>CONTACT TYPE</b>	Crimp
<b>COUPLING TYPE</b>	Push-Pull
<b>DEGREE OF PROTECTION</b>	IP40
<b>LAYOUT</b>	18
<b>PLATING</b>	Nickel Chrome
<b>PLUG TYPE</b>	Right Angle Plug
<b>SHELL MATERIAL</b>	Brass
<b>SHELL SIZE</b>	3
<b>MATING CYCLES</b>	5000
<b>OPERATING TEMPERATURE - MAX</b>	125 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C
<b>NUMBER OF CONTACTS</b>	18
<b>SALT SPRAY</b>	48 hour



---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:

---



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

