

Eaton

JBXFD3G18MSSDSMR

Straight plug, IP40, size3, 18 male contacts,
cable clamp protective boot;
JBXFD3G18MSSDSMR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXFD3G18MSSDSMR
PRODUCT LENGTH/DEPTH	61 mm
PRODUCT HEIGHT	16 mm
PRODUCT WIDTH	16 mm
PRODUCT WEIGHT	48.34 g
COMPLIANCES	UL 1977



CURRENT RATING	7 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
TEST CURRENT	7 A UL
TEST VOLTAGE	660 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Sealing Gland With Optional Boot
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Solder Cup
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	18
PLATING	Nickel Chrome
PLUG TYPE	Straight Plug
SHELL MATERIAL	Brass
SHELL SIZE	3
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	18
SALT SPRAY	48 hour



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

