

Eaton

JBXFF1G04FSNDSMR

Straight plug no latch, IP40, size 1, 4 female contacts, cable clamp protective boot;
JBXFF1G04FSNDSMR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXFF1G04FSNDSMR
PRODUCT LENGTH/DEPTH	68 mm
PRODUCT HEIGHT	12 mm
PRODUCT WIDTH	12 mm
PRODUCT WEIGHT	19.3 g
COMPLIANCES	UL 1977



CURRENT RATING	10 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	RoHS REACH
TEST CURRENT	10 A UL
TEST VOLTAGE	900 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Sealing Gland With Optional Boot
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Solder Cup
COUPLING TYPE	Push-Pull - Breakaway, no latch
DEGREE OF PROTECTION	IP40
LAYOUT	4
PLATING	Black Anodized
PLUG TYPE	Straight Plug
SHELL MATERIAL	Brass
SHELL SIZE	1
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	4
SALT SPRAY	96 hour



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

