

# Eaton

## JBXFH2G002FSNDSMR

Straight plug, IP68, size 2, 9 female contacts,  
cable clamp for protective boot;  
JBXFH2G002FSNDSMR

|                         |                                                                          |
|-------------------------|--------------------------------------------------------------------------|
|                         |                                                                          |
| PRODUCT NAME            | Eaton Souriau JBX series<br>IP40 / IP68 metallic push-<br>pull connector |
| CATALOG NUMBER          | JBXFH2G002FSNDSMR                                                        |
| PRODUCT<br>LENGTH/DEPTH | 52 mm                                                                    |
| PRODUCT HEIGHT          | 16 mm                                                                    |
| PRODUCT WIDTH           | 16 mm                                                                    |
| PRODUCT WEIGHT          | 28.64 g                                                                  |
| COMPLIANCES             | UL 1977                                                                  |



|                             |                                     |
|-----------------------------|-------------------------------------|
| CURRENT RATING              | 26 A UL                             |
| FITTED WITH:                | Shielding                           |
| ENVIRONMENTAL CONDITIONS    | REACH<br>RoHS                       |
| TEST CURRENT                | 26 A UL                             |
| TEST VOLTAGE                | 700 V UL                            |
| BACKSHELL ANGLE             | Straight                            |
| BACKSHELL TYPE              | Sealing Gland With<br>Optional Boot |
| CONNECTOR ACCESSORY OPTION  | Delivered with connector            |
| CONNECTOR TYPE              | Plug                                |
| CONTACT DELIVERY            | Loaded                              |
| CONTACT GENDER              | Socket (Female)                     |
| CONTACT TYPE                | Solder Cup                          |
| COUPLING TYPE               | Push-Pull                           |
| DEGREE OF PROTECTION        | IP68                                |
| LAYOUT                      | 2                                   |
| PLATING                     | Black Anodized                      |
| PLUG TYPE                   | Straight Plug                       |
| SHELL MATERIAL              | Brass                               |
| SHELL SIZE                  | 2                                   |
| MATING CYCLES               | 5000                                |
| OPERATING TEMPERATURE - MAX | 125 °C                              |
| OPERATING TEMPERATURE - MIN | -40 °C                              |
| NUMBER OF CONTACTS          | 9                                   |
| SALT SPRAY                  | 96 hour                             |



|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

