

Eaton

JBXFH2G05MCNDSR

Straight plug, IP68, size 2, 5 male contacts, cable clamp backshell; JBXFH2G05MCNDSR

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXFH2G05MCNDSR
PRODUCT LENGTH/DEPTH	52 mm
PRODUCT HEIGHT	16 mm
PRODUCT WIDTH	16 mm
PRODUCT WEIGHT	27.14 g
COMPLIANCES	UL 1977

CURRENT RATING	14 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	REACH RoHS
TEST CURRENT	14 A UL
TEST VOLTAGE	900 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP68
LAYOUT	5
PLATING	Black Anodized
PLUG TYPE	Straight Plug
SHELL MATERIAL	Brass
SHELL SIZE	2
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	5
SALT SPRAY	96 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

