



□□□□□

Eaton

JBXHH2G16MCNDSR

Front mount extended receptacle, IP68, size 2, 16 male contacts; JBXHH2G16MCNDSR

□□□□

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXHH2G16MCNDSR
PRODUCT LENGTH/DEPTH	29.5 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	18.64 g
COMPLIANCES	UL 1977

□□□□	
CURRENT RATING	6 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	REACH RoHS
TEST CURRENT	6 A UL
TEST VOLTAGE	730 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP68
LAYOUT	16
PLATING	Black Anodized
SHELL MATERIAL	Brass
SHELL SIZE	2
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Front Mount Panel
NUMBER OF CONTACTS	16
NUT MATERIAL	Aluminium
SALT SPRAY	96 hour

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□: