

Eaton

JBXSA2G04FCSDSM

Double nut receptacle, cable clamp protective boot, IP40, size 2, 4 female contacts; JBXSA2G04FCSDSM

PRODUCT NAME	Eaton Souriau JBX series IP40 / IP68 metallic push- pull connector
CATALOG NUMBER	JBXSA2G04FCSDSM
PRODUCT LENGTH/DEPTH	50 mm
PRODUCT HEIGHT	20 mm
PRODUCT WIDTH	20 mm
PRODUCT WEIGHT	30.54 g
COMPLIANCES	UL 1977

CURRENT RATING	15 A UL
FITTED WITH:	Shielding
ENVIRONMENTAL CONDITIONS	REACH RoHS
TEST CURRENT	15 A UL
TEST VOLTAGE	1000 V UL
BACKSHELL ANGLE	Straight
BACKSHELL TYPE	Sealing Gland With Optional Boot
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP40
LAYOUT	4
PLATING	Nickel Chrome
SHELL MATERIAL	Brass
SHELL SIZE	2
MATING CYCLES	5000
OPERATING TEMPERATURE - MAX	125 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Rear Mount Panel
NUMBER OF CONTACTS	4
NUT MATERIAL	Aluminium
SALT SPRAY	48 hour



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

