



Eaton JJN-400

Eaton Bussmann series JJN fuse, Current-limiting, VFD line protection, 400 A, Class T, Non-indicating, Bolted blade end x bolted blade end, 20 kAIC at 160 Vdc, 200 kAIC at 300 V, Standard, 1, 300 V, 160 Vdc

□□□□

PRODUCT NAME	Eaton Bussmann series JJN fuse
CATALOG NUMBER	JJN-400
UPC	051712627047
PRODUCT LENGTH/DEPTH	2.75 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.25 lb
COMPLIANCES	CE Marked

Specifications	
AMPERAGE RATING	400 A
INTERRUPT RATING	20 kAIC at 160 Vdc 200 kAIC at 300 Vac
VOLTAGE RATING	300 Vac, 160 Vdc

Details	
CLASS	Class T
CONNECTION	Bolted blade end x bolted blade end
FUSE INDICATOR	Non-indicating
QUANTITY	1

Packaging	
PACKAGING TYPE	Standard

Notes	
-------	--
