



□□□□□

## Eaton JJS-450

Eaton Bussmann series JJS fuse, Current-limiting, Small footprint, VFD line protection, 450 A, Class T, Non-indicating, Bolted blade end x bolted blade end, 200 kAIC at 600 V, Standard, 1, 600 V

### □□□□

|                             |                                |
|-----------------------------|--------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Bussmann series JJS fuse |
| <b>CATALOG NUMBER</b>       | JJS-450                        |
| <b>UPC</b>                  | 051712628211                   |
| <b>PRODUCT LENGTH/DEPTH</b> | 3.98 in                        |
| <b>PRODUCT HEIGHT</b>       | 1.25 in                        |
| <b>PRODUCT WIDTH</b>        | 1.25 in                        |
| <b>PRODUCT WEIGHT</b>       | 0.95 lb                        |
| <b>COMPLIANCES</b>          | CE Marked                      |

| Specifications   |                     |
|------------------|---------------------|
| AMPERAGE RATING  | 450 A               |
| INTERRUPT RATING | 200 kAIC at 600 Vac |
| VOLTAGE RATING   | 600 V               |

| Details          |                                     |
|------------------|-------------------------------------|
| CLASS            | Class T                             |
| CONNECTION       | Bolted blade end x bolted blade end |
| FUSE INDICATOR   | Non-indicating                      |
| QUANTITY         | 1                                   |
| SPECIAL FEATURES | Non-indicating                      |

| Packaging      |          |
|----------------|----------|
| PACKAGING TYPE | Standard |

| Notes |  |
|-------|--|
|-------|--|

|  |
|--|
|  |
|  |
|  |
|  |



Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

