



Eaton

JMXEP1A03FCUDSA

Push-pull plastic IP40 rear mount receptacle, layout 1-03, female crimp contacts, keying A, blue color coding; JMXEP1A03FCUDSA

□□□□

PRODUCT NAME	Eaton Souriau JMX series plastic push-pull connector
CATALOG NUMBER	JMXEP1A03FCUDSA
PRODUCT LENGTH/DEPTH	23.8 mm
PRODUCT HEIGHT	24 mm
PRODUCT WIDTH	24 mm
PRODUCT WEIGHT	6.8 g

CURRENT RATING	9 A UL 9 A IEC
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Unloaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Crimp
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP50
LAYOUT	3
SHELL MATERIAL	Plastic
SHELL SIZE	1
MATING CYCLES	2000
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-20 °C
RECEPTACLE TYPE	Rear Mount Panel
NUMBER OF CONTACTS	3

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: