



Eaton

JMXEP1A03FSUDSA

Push-pull plastic IP40 rear mount receptacle, layout 1-03, female solder contacts, keying A, blue color coding; JMXEP1A03FSUDSA

□□□□

PRODUCT NAME	Eaton Souriau JMX series plastic push-pull connector
CATALOG NUMBER	JMXEP1A03FSUDSA
PRODUCT LENGTH/DEPTH	23.8 mm
PRODUCT HEIGHT	24 mm
PRODUCT WIDTH	24 mm
PRODUCT WEIGHT	6.8 g

□□□□	
CURRENT RATING	9 A IEC 9 A UL
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR TYPE	Receptacle
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	Push-Pull
DEGREE OF PROTECTION	IP50
LAYOUT	3
SHELL MATERIAL	Plastic
SHELL SIZE	1
MATING CYCLES	2000
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-20 °C
RECEPTACLE TYPE	Rear Mount Panel
NUMBER OF CONTACTS	3

□□

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□

Follow us on social media to get the latest product and support information.

