



□□□□□

## Eaton JXD01020

Eaton xDetect modular addressable fire alarm system panel, JSB, Addressable, xDetect Control Panels, EN54 Systems, Small, Without ZI, , ,

□□□□

|                      |                             |
|----------------------|-----------------------------|
| PRODUCT NAME         | Eaton xDetect xDetect Small |
| CATALOG NUMBER       | JXD01020                    |
| PRODUCT LENGTH/DEPTH | 148 mm                      |
| PRODUCT HEIGHT       | 374 mm                      |
| PRODUCT WIDTH        | 426 mm                      |
| PRODUCT WEIGHT       | 8.4 kg                      |
| COMPLIANCES          | EN                          |

|                                               |                                                     |
|-----------------------------------------------|-----------------------------------------------------|
| <b>MOUNTING METHOD</b>                        | Surface mounting                                    |
| <b>OPERATING VOLTAGE</b>                      | 24 VDC                                              |
| <b>NUMBER OF BATTERIES</b>                    | 2                                                   |
| <b>BATTERY VOLTAGE</b>                        | 12 V                                                |
| <b>BATTERY CAPACITY</b>                       | 12 Ah                                               |
| <b>CLASS CHANGE CAPABILITY</b>                | Yes                                                 |
| <b>CONSTRUCTION MATERIAL BACK ENCLOSURE</b>   | Mild steel                                          |
| <b>CONSTRUCTION MATERIAL FRONT ENCLOSURE</b>  | Mild steel                                          |
| <b>HUMIDITY (NON CONDENSING) - MAX</b>        | 95 %                                                |
| <b>HUMIDITY (NON CONDENSING) - MIN</b>        | 0 %                                                 |
| <b>MAIN INPUT SUPPLY</b>                      | 230 Vac, 50 Hz                                      |
| <b>OPERATING TEMPERATURE - MAX</b>            | 50 °C                                               |
| <b>OPERATING TEMPERATURE - MIN</b>            | -5 °C                                               |
| <b>SYSTEM TOPOLOGY</b>                        | Addressable                                         |
| <b>MAXIMUM NETWORK SIZE (NUMBER OF NODES)</b> | 250                                                 |
| <b>TYPE OF DISPLAY</b>                        | Touchscreen                                         |
| <b>AUXILIARY FREE OUTPUT</b>                  | Yes                                                 |
| <b>AUXILIARY RELAYS</b>                       | Fire/Fault                                          |
| <b>PRODUCT BRANDING</b>                       | Eaton JSB                                           |
| <b>SUITABLE FOR</b>                           | Bus Connection                                      |
| <b>INTEGRATED FUNCTION</b>                    | Addressable<br>Interface External                   |
| <b>EN CERTIFICATION STANDARDS</b>             | EN54-2:1997+A1:2006,<br>EN54-4:1997+A1:2002+A2:2006 |
| <b>UL CERTIFICATION STANDARDS</b>             | Not Applicable                                      |
| <b>EXTERNAL CONNECTION PORTS</b>              | USB Mini-B 5 Pin                                    |

