



□□□□□

Eaton JXD01040

Eaton xDetect modular addressable fire alarm system panel, JSB, Addressable, xDetect Control Panels, EN54 Systems, Large, Without ZI, , ,

□□□□

PRODUCT NAME	Eaton xDetect xDetect Large
CATALOG NUMBER	JXD01040
PRODUCT LENGTH/DEPTH	148 mm
PRODUCT HEIGHT	527 mm
PRODUCT WIDTH	433 mm
PRODUCT WEIGHT	10.9 kg
COMPLIANCES	EN



Powering Business Worldwide

MOUNTING METHOD	Surface mounting
OPERATING VOLTAGE	24 VDC
NUMBER OF BATTERIES	2
BATTERY VOLTAGE	12 V
BATTERY CAPACITY	12 Ah
CLASS CHANGE CAPABILITY	Yes
CONSTRUCTION MATERIAL BACK ENCLOSURE	Mild steel
CONSTRUCTION MATERIAL FRONT ENCLOSURE	Mild steel
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
MAIN INPUT SUPPLY	230 Vac, 50 Hz
OPERATING TEMPERATURE - MAX	50 °C
OPERATING TEMPERATURE - MIN	-5 °C
SYSTEM TOPOLOGY	Addressable
MAXIMUM NETWORK SIZE (NUMBER OF NODES)	250
TYPE OF DISPLAY	Touchscreen
AUXILIARY FREE OUTPUT	Yes
AUXILIARY RELAYS	Fire/Fault
PRODUCT BRANDING	Eaton JSB
SUITABLE FOR	Bus Connection
INTEGRATED FUNCTION	Addressable Interface External
EN CERTIFICATION STANDARDS	EN54-2:1997+A1:2006, EN54-4:1997+A1:2002+A2:2006
UL CERTIFICATION STANDARDS	Not Applicable
EXTERNAL CONNECTION PORTS	USB Mini-B 5 Pin

