



□□□□□

Eaton LF1001-0004

Eaton LF Pressure Filter,
LF.1001.25VG.10.B.P.-.FS.A.-.AE.30.2,5.P.-.B,
25VG, Glass fiber fleece (VG), Nitrile, 464 psi
(32 Bar), Non-bypass

□□□□

PRODUCT NAME	Eaton LF Pressure Filter
CATALOG NUMBER	LF1001-0004
PRODUCT LENGTH/DEPTH	260.99 mm
PRODUCT HEIGHT	586.52 mm
PRODUCT WIDTH	219.99 mm
PRODUCT WEIGHT	47.18 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000



Powering Business Worldwide

0000

CONNECTION TYPE	3" SAE/ANSI flange
DESIGN	Double open end
FILTER TYPE	In-line Filter Low pressure filter
MATERIAL	EN-GJS-400-18-LT
APPLICATION	Mounted in suction, pressure and return lines
SPECIFICATION	Standard
FILTER FINENESS	25 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Nitrile
ELEMENT COLLAPSE RATING	145 psi (10 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Non-bypass
OPERATING PRESSURE - MAX	464 psi (32 Bar)

00

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
00:



0000
Eaton House
30 Pembroke Road
Dublin 4, 0000
Eaton.com

© 2025 00 00000000

Follow us on social media to get the latest product and support information.

