



□□□□□

Eaton LF1001-0014

Eaton LF Pressure Filter,
LF1001.10VG.10.B.V.-.FS.A.-.S.-, 10 VG, Glass
fiber fleece (VG), Viton, 464 psi (32 Bar),
Bypass set at 29 psi (2 Bar)

□□□□

PRODUCT NAME	Eaton LF Pressure Filter
CATALOG NUMBER	LF1001-0014
PRODUCT LENGTH/DEPTH	220 mm
PRODUCT HEIGHT	586.5 mm
PRODUCT WIDTH	212 mm
PRODUCT WEIGHT	47.17 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000

CONNECTION TYPE	3" SAE/ANSI flange
FILTER TYPE	Low pressure filter
MATERIAL	EN-GJS-400-18-LT
RETENTION RATING	5.0 μ m
APPLICATION	Mounted in suction, pressure and return lines
SPECIFICATION	Standard
CODE STAMP	None
FILTER FINENESS	10 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	None
SEALING MATERIAL	Viton
ELEMENT COLLAPSE RATING	145 psi (10 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Bypass set at 29 psi (2 Bar)
OPERATING PRESSURE - MAX	464 psi (32 Bar)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: