



□□□□□

Eaton LF1001-0017

Eaton LF Pressure Filter,
LF1001.10VG.10.B.V.-.FS.A.-.S1.AE.30.2,5.V.-
.B, 10 VG, Glass fiber fleece (VG), Viton, 464
psi (32 Bar), Bypass set at 51 psi (3.5 Bar)

□□□□

PRODUCT NAME	Eaton LF Pressure Filter
CATALOG NUMBER	LF1001-0017
PRODUCT LENGTH/DEPTH	262.02 mm
PRODUCT HEIGHT	586.52 mm
PRODUCT WIDTH	219.99 mm
PRODUCT WEIGHT	47.17 kg
COMPLIANCES	PED 2014/68/EU for mineral oil (fluid group 2), Article 4, Para. 3. ATEX Directive 2014/34/EU AD 2000



Powering Business Worldwide

CONNECTION TYPE	3" SAE/ANSI flange
FILTER TYPE	Low pressure filter
MATERIAL	EN-GJS-400-18-LT
RETENTION RATING	7.0 μ m
APPLICATION	Mounted in suction, pressure and return lines
SPECIFICATION	Standard
CODE STAMP	None
FILTER FINENESS	10 VG
FILTER MEDIA TYPE	Glass fiber fleece (VG)
FLUID GROUP (DGRL 2014/68/EU)	2
INDICATOR TYPE	Electrical/Visual
SEALING MATERIAL	Viton
ELEMENT COLLAPSE RATING	145 psi (10 Bar)
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-10 °C
VALVE CONFIGURATION OPTIONS	Bypass set at 51 psi (3.5 Bar)
OPERATING PRESSURE - MAX	464 psi (32 Bar)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: