



□□□□□

Eaton LZ48G28E09CUTC

9 kVA Class 1 Division 2 Transformer, ABS, 3PH, 480-208Y/120, Three-coil, shielded, Copper Windings, NEMA 3R Enclosure

□□□□

PRODUCT NAME	Eaton Hazardous location encapsulated transformer
CATALOG NUMBER	LZ48G28E09CUTC
UPC	786680233548
PRODUCT LENGTH/DEPTH	1.1 in
PRODUCT HEIGHT	1.1 in
PRODUCT WIDTH	1.1 in
PRODUCT WEIGHT	1.1 lb
COMPLIANCES	Class I, Div. 2, Groups A, B, C, D
CERTIFICATIONS	UL Listed ABS Certified



Powering Business Worldwide

SPECIAL FEATURES	Shielded
TYPE	Class 1 Division 2 Groups A, B, C and D, Hazardous Location Transformer, ABS Marine Duty
AREA CLASSIFICATION	Hazardous/Classified Locations
COIL MATERIAL	Copper
FREQUENCY RATING	50/60 Hz
KVA RATING	9 kVA
KVA	9 kVA
PHASE	Three-phase
PRIMARY VOLTAGE	480 V
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	115 °C rise
ENCLOSURE	NEMA 3R
INSULATION	180 °C
MODIFICATION 1	ABS marine duty
TAP SIZE	2 at -5% FCBN
VOLT AMPERE RATING	9 kVA
WEATHERSHIELD	Indoor-Outdoor

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: