



## Eaton M100-003-BK

USB-A to Lightning Sync/Charge Cable, MFi Certified - Black, M/M, USB 2.0, 3 ft. (0.91 m)



<b>PRODUCT NAME</b>	Eaton Tripp Lite series cable
<b>CATALOG NUMBER</b>	M100-003-BK
<b>UPC</b>	037332182159
<b>PRODUCT LENGTH/DEPTH</b>	2.36 in
<b>PRODUCT HEIGHT</b>	0.91 in
<b>PRODUCT WIDTH</b>	4.57 in
<b>PRODUCT WEIGHT</b>	0.04 lb
<b>COMPLIANCES</b>	RoHS REACH UKCA
<b>CERTIFICATIONS</b>	MFi



Powering Business Worldwide



<b>AMPERAGE RATING</b>	2A
<b>OPERATING HUMIDITY RANGE</b>	0% to 90% RH, Non-Condensing
<b>STORAGE HUMIDITY RANGE</b>	0% to 90% RH, Non-Condensing
<b>CABLE JACKET RATING</b>	VW-1
<b>CABLE JACKET COLOR</b>	Black
<b>CONNECTOR PLATING</b>	Nickel
<b>CONNECTOR TYPE</b>	USB/Thunderbolt/Lightning
<b>USB SPECIFICATION</b>	USB 2.0 (up to 480 Mbps)
<b>CABLE JACKET MATERIAL</b>	PVC
<b>CONNECTOR STYLE</b>	Straight
<b>PACKAGE CONTENTS</b>	M100-003-BK USB-A to Lightning Sync/Charge Cable (M/M), Black, 3 ft. (0.9 m)
<b>PRODUCT HIGHLIGHTS</b>	USB plug connects to USB-A port on computer or charger MFi-certified for use with iPhone, iPad and iPod devices Reversible Lightning plug compatible with all devices with 8-pin connectors
<b>CONTACT PLATING</b>	Gold
<b>SIDEA CONNECTOR1</b>	USB A (MALE)
<b>SIDEB CONNECTOR1</b>	LIGHTNING (MALE)
<b>OPERATING TEMPERATURE</b>	-4° to 140°F (-20° to 60°C)
<b>OPERATING TEMPERATURE RANGE</b>	-4° to 140°F (-20° to 60°C)
<b>STORAGE TEMPERATURE RANGE</b>	-4° to 176°F (-20° to 80°C)
<b>SIDEB CONNECTOR3</b>	LIGHTNING (MALE)
<b>TECHNOLOGY</b>	Lightning USB 2.0 (High Speed)
<b>DATA TRANSFER RATE</b>	480 Mbps
<b>CABLE LENGTH</b>	Up to 4ft (up to 1M)
<b>CABLE OUTER DIAMETER (OD)</b>	2.8mm
<b>CABLE TYPE</b>	Passive
<b>CONNECTOR GROUP</b>	Lightning USB-A
<b>MATERIAL</b>	PVC
<b>WIRE GAUGE (AWG)</b>	30/24

