



Eaton M100-003-WH

USB-A to Lightning Sync/Charge Cable, MFi Certified - White, M/M, USB 2.0, 3 ft. (0.91 m)



PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	M100-003-WH
UPC	037332182173
PRODUCT LENGTH/DEPTH	0.05 in
PRODUCT HEIGHT	4.57 in
PRODUCT WIDTH	2.36 in
PRODUCT WEIGHT	0.08 lb
COMPLIANCES	RoHS REACH UKCA
CERTIFICATIONS	MFi



Powering Business Worldwide



AMPERAGE RATING	2A
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	White
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	M100-003-WH USB-A to Lightning Sync/Charge Cable (M/M), White, 3 ft. (0.9 m)
PRODUCT HIGHLIGHTS	MFi-certified for use with iPhone, iPad and iPod devices Reversible Lightning plug compatible with all devices with 8-pin connectors USB plug connects to USB-A port on computer or charger
CONTACT PLATING	Gold
SIDE A CONNECTOR1	USB A (MALE)
SIDE B CONNECTOR1	LIGHTNING (MALE)
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
SIDE B CONNECTOR3	LIGHTNING (MALE)
TECHNOLOGY	Lightning USB 2.0 (High Speed)
DATA TRANSFER RATE	480 Mbps
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	2.8mm
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A Lightning
MATERIAL	PVC
WIRE GAUGE (AWG)	30/24

