



Eaton M100-004COIL-BK

USB-A to Lightning Sync/Charge Coiled Cable, MFi Certified - Black, M/M, USB 2.0, 4 ft. (1.22 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	M100-004COIL-BK
UPC	037332192110
PRODUCT LENGTH/DEPTH	0.91 in
PRODUCT HEIGHT	4.57 in
PRODUCT WIDTH	2.4 in
PRODUCT WEIGHT	0.04 lb
COMPLIANCES	RoHS REACH UKCA
CERTIFICATIONS	MFi



Powering Business Worldwide



AMPERAGE RATING	2A
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	M100-006-BK USB-A to Lightning Sync/Charge Coiled Cable (M/M), Black, 4 ft. (1.2 m)
PRODUCT HIGHLIGHTS	4 ft. cable is coiled to take up less space and avoid cord clutter USB plug connects to USB-A port on computer or charger Effective length of 2 to 3 ft. when in use Reversible Lightning plug compatible with all devices with 8-pin connectors MFi-certified for use with iPhone, iPad and iPod devices
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	LIGHTNING (MALE)
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
SIDEB CONNECTOR3	LIGHTNING (MALE)
TECHNOLOGY	Lightning USB 2.0 (High Speed)
DATA TRANSFER RATE	480 Mbps
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	3.8mm
CABLE TYPE	Passive

