



Eaton M100-006-BK

USB-A to Lightning Sync/Charge Cable, MFi Certified - Black, M/M, USB 2.0, 6 ft. (1.83 m)



PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	M100-006-BK
UPC	037332182166
PRODUCT LENGTH/DEPTH	2.6 in
PRODUCT HEIGHT	5.3 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	0.09 lb
COMPLIANCES	REACH RoHS UKCA
CERTIFICATIONS	MFi



Powering Business Worldwide



AMPERAGE RATING	2A
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	M100-006-BK USB-A to Lightning Sync/Charge Cable (M/M), Black, 6 ft. (1.8 m)
PRODUCT HIGHLIGHTS	MFi-certified for use with iPhone, iPad and iPod devices Reversible Lightning plug compatible with all devices with 8-pin connectors USB plug connects to USB-A port on computer or charger
CONTACT PLATING	Gold
SIDE A CONNECTOR1	USB A (MALE)
SIDE B CONNECTOR1	LIGHTNING (MALE)
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
SIDE B CONNECTOR3	LIGHTNING (MALE)
TECHNOLOGY	Lightning USB 2.0 (High Speed)
DATA TRANSFER RATE	480 Mbps
CABLE LENGTH	5 - 8ft (1 - 2M)
CABLE OUTER DIAMETER (OD)	3.2mm
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A Lightning
MATERIAL	PVC
WIRE GAUGE (AWG)	28/21

