



Eaton M100-10N-BK-10

USB-A to Lightning Sync/Charge Cable, MFi Certified - Black, M/M, USB 2.0, 10 Pack - 10 in. (0.3m)



PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	M100-10N-BK-10
UPC	037332188526
PRODUCT LENGTH/DEPTH	2.5 in
PRODUCT HEIGHT	5.25 in
PRODUCT WIDTH	2.5 in
PRODUCT WEIGHT	0.25 lb
COMPLIANCES	REACH RoHS UKCA
CERTIFICATIONS	MFi



Powering Business Worldwide




AMPERAGE RATING	2A
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	Black
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	(10) M100-10N-BK USB-A to Lightning Sync/Charge Cables (M/M), Black, 10 in. (0.25 m)
PRODUCT HIGHLIGHTS	USB plugs connect to USB-A port on computer or charger Reversible Lightning plugs compatible with all devices with 8-pin connectors Includes ten M100-10N-BK charge/sync cables MFi-certified for use with iPhone, iPad and iPod devices
CONTACT PLATING	Gold
SIDE A CONNECTOR1	USB A (MALE)
SIDE B CONNECTOR1	LIGHTNING (MALE)
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
SIDE B CONNECTOR3	LIGHTNING (MALE)
TECHNOLOGY	Lightning USB 2.0 (High Speed)
DATA TRANSFER RATE	480 Mbps
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	2.8mm
CABLE TYPE	Passive
CONNECTOR GROUP	Lightning USB-A

MATERIAL	PVC
WIRE GAUGE (AWG)	30/24
POWER PROVIDED TO CONNECTED DEVICE(S)	12W (5V/2.4A)
TOTAL CHARGING WATTS	12 W
CABLE LENGTH RANGE	Up to 4ft (up to 1M)
CONNECTOR	USB A (male) Lightning (male)

□□□□:
□□□□:
□□□:
□□:



□□□□ Eaton House
 30 Pembroke Road
 Dublin 4, □□□
 Eaton.com



© 2026 □□ □□□□□□□□