



Eaton M110-003-WH

USB Sync/Charge Cable with Apple 30-Pin Dock Connector, White, 3 ft. (0.91 m)



PRODUCT NAME	Eaton Tripp Lite series cable
CATALOG NUMBER	M110-003-WH
UPC	037332190062
PRODUCT LENGTH/DEPTH	2.6 in
PRODUCT HEIGHT	5.2 in
PRODUCT WIDTH	0.9 in
PRODUCT WEIGHT	0.05 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	MFi



Powering Business Worldwide



AMPERAGE RATING	2A
OPERATING HUMIDITY RANGE	0% to 90% RH, Non-Condensing
RELATIVE HUMIDITY	0-90% non-condensing
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	VW-1
CABLE JACKET COLOR	White
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	USB/Thunderbolt/Lightning Mobile devices
USB SPECIFICATION	USB 2.0 (up to 480 Mbps)
CABLE JACKET MATERIAL	PVC
CONNECTOR STYLE	Straight
PACKAGE CONTENTS	M110-003-WH USB Sync/Charge Cable with Apple 30-Pin Dock Connector
PRODUCT HIGHLIGHTS	MFi-certified for broad compatibility with your Apple iPhone, iPad or iPod Compatible with all Apple devices with 30-pin connectors Features an Apple-compatible 30-pin plug and a USB-A plug Works with any computer
CONTACT PLATING	Gold
SIDEA CONNECTOR1	USB A (MALE)
SIDEB CONNECTOR1	30 PIN APPLE (MALE)
OPERATING TEMPERATURE	-4° to 140°F (-20° to 60°C)
OPERATING TEMPERATURE RANGE	-4° to 140°F (-20° to 60°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
SIDEB CONNECTOR3	30 PIN APPLE (MALE)
TECHNOLOGY	USB 2.0 (High Speed)
DATA TRANSFER RATE	480 Mbps
CABLE LENGTH	Up to 4ft (up to 1M)
CABLE OUTER DIAMETER (OD)	2.8mm
CABLE TYPE	Passive
CONNECTOR GROUP	USB-A

