



Eaton MAS850LPSWP

Eaton Addressable sounder, Menvier, Addressable, Sounder, EN54 Systems, Wall Mounted, Red Plastic, Weatherproof

□□□□

PRODUCT NAME	Eaton Addressable sounder
CATALOG NUMBER	MAS850LPSWP
PRODUCT LENGTH/DEPTH	103 mm
PRODUCT HEIGHT	108 mm
PRODUCT WIDTH	109 mm
PRODUCT WEIGHT	0.32 kg
CERTIFICATIONS	Not Applicable



Powering Business Worldwide



NUMBER OF TONES	4
COLOR HOUSING	Red
MATERIAL HOUSING	Plastic
SOUND OUTPUT	100 dB
NOMINAL VOLTAGE	28 VDC
TYPE OF CURRENT	DC
ELECTRICITY CONSUMPTION	0.006 A
ADDRESSING MODE	Soft addressing
ALARM CURRENT	6 mA
CONSTRUCTION MATERIAL	ABS
EN CERTIFIED TONES	4
OPERATING TEMPERATURE - MAX	55 °C
OPERATING TEMPERATURE - MIN	-10 °C
STANDBY CURRENT	320
SYSTEM TOPOLOGY	Addressable
VOICE TONES	No
PRODUCT BRANDING	Eaton Menvier
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
DEGREE OF PROTECTION	IP66
EN CERTIFICATION STANDARDS	EN54 Pt3 (Fire Alarm Sounders) EN54 Pt17 (Short Circuit Isolator)
CABLE ENTRY	Rear
SYSTEM WIRING	2.5 mm



