



Eaton MBP11K208

Eaton 9PX maintenance bypass, 3U,
Hardwired input, Outputs: (3) L6-30R,
Hardwired

□□□□

PRODUCT NAME	Eaton 9PX maintenance bypass
CATALOG NUMBER	MBP11K208
UPC	743172043610
PRODUCT LENGTH/DEPTH	8.7 in
PRODUCT HEIGHT	5.1 in
PRODUCT WIDTH	13.2 in
PRODUCT WEIGHT	13.7 lb
COMPLIANCES	CE Marked
CERTIFICATIONS	IEC 61000-4-5 EN 61000-4-4 Electrical fast transient IEC/EN 62040-2 EN 61000-4-2 IEC/EN 62040-1 EN 61000-4-3 EN 62040-3 IEC 61000-4-6 IEC 61000-4-7 cULus Listed NOM ICC-ES AC156 OSHPD Seismic certified

□□□□	
SPECIAL FEATURES	Rear mount, Rackmount
RACK SIZE	3U
COLOR	Black/silver
PACKAGE CONTENTS	• MBP11K208 Maintenance Bypass • (2) Input/output covers • Input/output cover fixation kit • (2) Conduits for UPS input/output connection • (4) Conduit fittings • Mounting hardware • Installation and user manual
USED WITH	9PX 8-11K 208V models
INPUT CONNECTION	Hardwired
RECEPTACLE	(3) L6-30R, Hardwired
STANDARD FACTORY WARRANTY	• 3-YEAR FACTORY WARRANTY • - 3 years • - Parts, electronics and batteries coverage • - Standard ground shipping • - Technical support
RELATIVE HUMIDITY	0-95% non-condensing
TEMPERATURE RANGE	0° to 40°C (32° to 104°F)
ACCESSORY CLASS	UPS Accessories
ACCESSORY TYPE	Bypass Panel (Rack-Mount)

□□	
□□□□□□□□	Eaton Specification Sheet - MBP11K208

