



Eaton MBP11K208G2

Eaton 9PX Gen 2 Maintenance bypass, Input: Hardwired, Output: Hardwired, (4) L6-30R, 0U rear mount



PRODUCT NAME	Eaton 9PX maintenance bypass
CATALOG NUMBER	MBP11K208G2
UPC	786689876074
PRODUCT LENGTH/DEPTH	5.12 in
PRODUCT HEIGHT	5.12 in
PRODUCT WIDTH	11.22 in
PRODUCT WEIGHT	10.14 lb
COMPLIANCES	CE Marked
CERTIFICATIONS	IEC/EN 62040-2 EN 61000-4-2 IEC/EN 62040-1 EN 61000-4-3 EN 62040-3 IEC 61000-4-6 IEC 61000-4-5 EN 61000-4-4 Electrical fast transient IEC 61000-4-7 cULus Listed NOM ICC-ES AC156 OSHPD Seismic certified



Powering Business Worldwide

□□□□

RACK SIZE 0U

COLOR Black/silver

RACK MOUNTING KIT Yes

PACKAGE CONTENTS

- MBP11K208G2 Maintenance Bypass
- (2) Input/output covers
- Input/output cover fixation kit
- (2) Conduits for UPS input/output connection
- (4) Conduit fittings
- Mounting hardware

INPUT CONNECTION Hardwired

RECEPTACLE (4) L6-30R, Hardwired

NUMBER OF OUTPUTS L6-30R 4

STANDARD FACTORY WARRANTY

- 3-YEAR FACTORY WARRANTY
- - 3 years
- - Parts, electronics and batteries coverage
- - Standard ground shipping
- - Technical support

RELATIVE HUMIDITY 0-95% non-condensing

TEMPERATURE RANGE 0° to 40°C (32° to 104°F)

ACCESSORY CLASS UPS Accessories

ACCESSORY TYPE Bypass Panel (Rack-Mount)

□□

