



Eaton MBP20KIPDU

Eaton 20 kW Maintenance Bypass Module with integrated distribution, 3U, rack or tower mount

□□□□

PRODUCT NAME	Eaton 93PX UPS
CATALOG NUMBER	MBP20KIPDU
PRODUCT LENGTH/DEPTH	592 mm
PRODUCT HEIGHT	129 mm
PRODUCT WIDTH	438 mm
PRODUCT WEIGHT	13.6 kg
COMPLIANCES	CE Marked RoHS Compliant CB
CERTIFICATIONS	IEC/EN 62040-2 IEC/EN 62040-1 EN 62040-3 Manufactured in a plant certified to ISO 9001 and ISO 14001 management system standards



Powering Business Worldwide

AUTO SHUTDOWN FUNCTION	No
INTERNAL BATTERY INCLUDED	No
COLOR	Black
CONSTRUCTION TYPE	482.6 mm (19 inch) device
FORM FACTOR	Rack/tower
INPUT CONNECTION	Fixed connection
NUMBER OF OUTPUT CONNECTIONS C13	6
NUMBER OF OUTPUT CONNECTIONS C19	3
NUMBER OF OUTPUT CONNECTIONS FIXED CONNECTION	1
POTENTIAL FREE SWITCH CONTACT	No
RACK SIZE	3U
SNMP	No
INTERNAL MAINTENANCE BYPASS	Yes
NUMBER OF OUTPUT CONNECTIONS WITH PROTECTIVE CONTACT (SCHUKO)	0
APPLICATION	Data center/ facility/IT
COMMUNICATION INTERFACE	USB RS232
MOUNTING METHOD	Tower Rackmount
NUMBER OF OUTPUT CONNECTIONS FRENCH STANDARD (TYPE E)	0

