



□□□□□

Eaton MBP3KIB

Eaton HotSwap MBP maintenance bypass,
3000 VA, BS, Input: C20, 200-240V, Outlets:
(3) BS, (1) C19

□□□□

PRODUCT NAME	Eaton HotSwap MBP maintenance bypass
CATALOG NUMBER	MBP3KIB
PRODUCT LENGTH/DEPTH	76.5 mm
PRODUCT HEIGHT	50 mm
PRODUCT WIDTH	439 mm
PRODUCT WEIGHT	2.1 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	CE

TYPE	Hotswap MBP
FORM FACTOR	1U
OUTLET CONTROL	No
PACKAGE CONTENTS	• Maintenance Bypass • Cable locking system • Connection cable to the UPS • Rack-mounting kit • User manual
OPERATING TEMPERATURE	0° to 40°C (32° to 104°F)
MOUNTING DIRECTION	Horizontal/vertical
COLOR	Black
INPUT CONNECTION	C20
VA RATING	3000 VA
INPUT VOLTAGE	200-240V
PHASE	Single-phase
OUTLETS	(3) BS, (1) C19
NUMBER OF OUTPUTS C19	1
NUMBER OF OUTLETS WITH EARTH PIN	4
NUMBER OF UK BS1363 SOCKETS	3
SNMP	No
ETHERNET INTERFACE	No
SERIAL INTERFACE	No
MASS CONFIGURATION	No
ELECTRICAL CONNECTION	Socket outlet
MOUNTING DIMENSION (METRICAL)	50
MOUNTING DIMENSION (STANDARDIZED)	482.6 mm (19 inch)
SWITCHABLE	No
OVER VOLTAGE CATEGORY	2
FITTED WITH:	LED indication Mounting material
COMMUNICATION	No

