



□□□□□

## Eaton MBP3KID

Eaton HotSwap MBP maintenance bypass,  
3000 VA, DIN, Input: C20, 200-240V, Outlets:  
(4) Schuko/DIN, (1) C19

□□□□

|                             |                                      |
|-----------------------------|--------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton HotSwap MBP maintenance bypass |
| <b>CATALOG NUMBER</b>       | MBP3KID                              |
| <b>PRODUCT LENGTH/DEPTH</b> | 76.5 mm                              |
| <b>PRODUCT HEIGHT</b>       | 50 mm                                |
| <b>PRODUCT WIDTH</b>        | 439 mm                               |
| <b>PRODUCT WEIGHT</b>       | 2.134 kg                             |
| <b>COMPLIANCES</b>          | CE Marked                            |
| <b>CERTIFICATIONS</b>       | CE                                   |

|                                   |                                                                                                                                                                                             |
|-----------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| □□□□                              |                                                                                                                                                                                             |
| TYPE                              | Hotswap MBP                                                                                                                                                                                 |
| FORM FACTOR                       | 1U                                                                                                                                                                                          |
| OUTLET CONTROL                    | No                                                                                                                                                                                          |
| PACKAGE CONTENTS                  | <ul style="list-style-type: none"><li>• Maintenance Bypass</li><li>• Cable locking system</li><li>• Connection cable to the UPS</li><li>• Rack-mounting kit</li><li>• User manual</li></ul> |
| OPERATING TEMPERATURE             | 0° to 40°C (32° to 104°F)                                                                                                                                                                   |
| MOUNTING DIRECTION                | Horizontal/vertical                                                                                                                                                                         |
| COLOR                             | Black                                                                                                                                                                                       |
| INPUT CONNECTION                  | C20                                                                                                                                                                                         |
| VA RATING                         | 3000 VA                                                                                                                                                                                     |
| INPUT VOLTAGE                     | 200-240V                                                                                                                                                                                    |
| PHASE                             | Single-phase                                                                                                                                                                                |
| OUTLETS                           | (4) Schuko, (1) C19                                                                                                                                                                         |
| NUMBER OF OUTPUTS C19             | 1                                                                                                                                                                                           |
| NUM OF OUTPUTS PC (SCHUKO)        | 4                                                                                                                                                                                           |
| NUMBER OF OUTLETS WITH EARTH PIN  | 5                                                                                                                                                                                           |
| SNMP                              | No                                                                                                                                                                                          |
| ETHERNET INTERFACE                | No                                                                                                                                                                                          |
| SERIAL INTERFACE                  | No                                                                                                                                                                                          |
| MASS CONFIGURATION                | No                                                                                                                                                                                          |
| ELECTRICAL CONNECTION             | Socket outlet                                                                                                                                                                               |
| EVALUATION                        | Other                                                                                                                                                                                       |
| MOUNTING DIMENSION (METRICAL)     | 50                                                                                                                                                                                          |
| MOUNTING DIMENSION (STANDARDIZED) | 482.6 mm (19 inch)                                                                                                                                                                          |
| SWITCHABLE                        | No                                                                                                                                                                                          |
| OVER VOLTAGE CATEGORY             | 2                                                                                                                                                                                           |
| AMPEREMETER                       | No                                                                                                                                                                                          |
| FITTED WITH:                      | Mounting material<br>LED indication                                                                                                                                                         |
| COMMUNICATION                     | No                                                                                                                                                                                          |

|    |
|----|
| □□ |
|----|

