



□□□□□

Eaton MBP3KIH

Eaton HotSwap MBP maintenance bypass,
3000 VA, HW, Input: Hardwired, 200-240V,
Outlets: Hardwired

□□□□

PRODUCT NAME	Eaton HotSwap MBP maintenance bypass
CATALOG NUMBER	MBP3KIH
PRODUCT LENGTH/DEPTH	76.5 mm
PRODUCT HEIGHT	50 mm
PRODUCT WIDTH	439 mm
PRODUCT WEIGHT	2 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	CE

□□□□	
TYPE	Hotswap MBP
FORM FACTOR	1U
OUTLET CONTROL	No
PACKAGE CONTENTS	• Maintenance Bypass • Cable locking system • Connection cable to the UPS • Rack-mounting kit • User manual
OPERATING TEMPERATURE	0° to 40°C (32° to 104°F)
MOUNTING DIRECTION	Horizontal/vertical
COLOR	Black
INPUT CONNECTION	Other
VA RATING	3000 VA
INPUT VOLTAGE	200-240V
PHASE	Single-phase
OUTLETS	Hardwired
NUMBER OF OUTPUTS HARDWIRED	1
SNMP	No
ETHERNET INTERFACE	No
SERIAL INTERFACE	No
MASS CONFIGURATION	No
ELECTRICAL CONNECTION	Screwed terminal
EVALUATION	Other
MOUNTING DIMENSION (METRICAL)	50
MOUNTING DIMENSION (STANDARDIZED)	482.6 mm (19 inch)
SWITCHABLE	No
OVER VOLTAGE CATEGORY	2
AMPEREMETER	No
FITTED WITH:	Mounting material LED indication
COMMUNICATION	No



