



Eaton MBP6KIECG2

Eaton 9PX Gen 2 Maintenance bypass, Input: Hardwired, Output: Hardwired, (3) C39, (2) C13, 0U rear mount

□□□□

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton 9PX maintenance bypass |
| CATALOG NUMBER | MBP6KIECG2 |
| UPC | 786689876067 |
| PRODUCT LENGTH/DEPTH | 4.92 in |
| PRODUCT HEIGHT | 5.12 in |
| PRODUCT WIDTH | 9.41 in |
| PRODUCT WEIGHT | 5.29 lb |
| COMPLIANCES | CE Marked |
| CERTIFICATIONS | EN 61000-4-3 IEC 61000-4-6 IEC 61000-4-5 EN 61000-4-2 IEC/EN 62040-1 IEC/EN 62040-2 EN 61000-4-4 Electrical fast transient EN 62040-3 cULus Listed NOM IEC 61000-4-8 |



Powering Business Worldwide

□□□□

| | |
|----------------------------------|--|
| RACK SIZE | 0U |
| COLOR | Black/silver |
| RACK MOUNTING KIT | Yes |
| PACKAGE CONTENTS | <ul style="list-style-type: none">• MBP6KIECG2 Maintenance Bypass• Input/output UPS cable set• (2) Cable glands• Mounting hardware |
| INPUT CONNECTION | L6-30P and hardwire input supported |
| RECEPTACLE | <ul style="list-style-type: none">• (2) C13, (3) C39• C39 combo outlets accept C14 and C20 connectors |
| NUMBER OF OUTPUTS C13 | 2 |
| STANDARD FACTORY WARRANTY | <ul style="list-style-type: none">• 3-YEAR FACTORY WARRANTY• - 3 years• - Parts and electronics• - Standard ground shipping• - Technical support |
| RELATIVE HUMIDITY | 0-95% non-condensing |
| TEMPERATURE RANGE | 0° to 40°C (32° to 104°F) |
| ACCESSORY CLASS | UPS Accessories |
| ACCESSORY TYPE | Bypass Panel (Rack-Mount) |

□□

