



□□□□□

Eaton ML3A4WC030F

Eaton Crouse-Hinds series LynxPOWER Mini-Line cordset, 13A, ST00W cable, #16 AWG, Male, straight plug, internal thread, pigtail, Passive, Zinc, Three-pole, Style I, 3 ft cable length

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series LynxPOWER Mini-Line cordset
CATALOG NUMBER	ML3A4WC030F
UPC	662275945549
PRODUCT LENGTH/DEPTH	1.93 in
PRODUCT HEIGHT	1 in
PRODUCT WIDTH	1 in
PRODUCT WEIGHT	1 lb

0000	
AREA CLASSIFICATION	Ordinary/Non-Hazardous Locations
STANDARDS TYPE	NEC/CEC IEC
NEMA RATING	4
	13
	1
	6P
	3
INGRESS PROTECTION (IP) RATINGS	IP68
AMPERAGE RATING	13 A
NUMBER OF POLES	Three-pole
CABLE/WIRE SIZE	#16 AWG
CABLE TYPE	STOOW
CABLE LENGTH	3 ft
CONNECTOR TYPE	Passive
GENDER	Male
MATERIAL	Zinc
STYLE	Style I
CONFIGURATION	Male, straight plug, internal thread, pigtail

00	
00000000	Eaton Specification Sheet - ML3A4WC030F
0000	LynxPower industrial connectivity solutions
0000	Mini-Line and Micro-Mini Cordsets, Receptacles and Multi-port Boxes catalog page

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: