



□□□□□

Eaton MLLA2-UNV1-EM1-M2

Eaton Crouse-Hinds series Champ MLLA linear LED, Cool white, 3/4" entries, Natural alum finish, 2 ft, Clear glass lens, 4000 lm, 132 lm/W, Copper-free alum, Flush ceil mt, Wide, >0.92 PF, Battery back-up, 120-277 Vac, 127/250 Vdc, 30W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ MLLA linear LED light fixture
CATALOG NUMBER	MLLA2-UNV1-EM1-M2
UPC	786689793937
PRODUCT LENGTH/DEPTH	25.94 in
PRODUCT HEIGHT	4.42 in
PRODUCT WIDTH	7.13 in
PRODUCT WEIGHT	19.1 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Zone 2 Class III Class I, Division 2 Class II, Division 1
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66 IP67

Product specifications

LAMP TYPE	LED
COLOR TEMPERATURE	Cool white
LAMP LENGTH	2 ft
LUMENS	4000
LUMENS PER WATT	132
OPTICAL DISTRIBUTION	Wide
MOUNTING METHOD	Flush ceiling
VOLTAGE RATING	120-277 Vac, 127/250 Vdc
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Glass
ENTRY SIZE	3/4"
FINISH	Natural aluminum
MATERIAL	Copper-free aluminum
WATTAGE	30W
POWER FACTOR	> 0.92
SPECIAL FEATURES	Integral emergency battery back-up

0000:	
0000:	
000:	
00:	