



□□□□□

Eaton MLLA2-UNV1-S903-EM1-M2

Eaton Crouse-Hinds series Champ MLLA linear LED, Cool white, 3/4" entries, Natural alum finish, 2 ft, Polycarb lens, 4000 lm, 132 lm/W, Copper-free alum, Flush ceil mt, Wide, >0.92 PF, Integral emerg battery, 120-277 Vac, 127/250 Vdc, 30W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ MLLA linear LED light fixture
CATALOG NUMBER	MLLA2-UNV1-S903-EM1-M2
UPC	786689716745
PRODUCT LENGTH/DEPTH	25.94 in
PRODUCT HEIGHT	4.42 in
PRODUCT WIDTH	7.13 in
PRODUCT WEIGHT	19.1 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP67 IP66

Product specifications

LAMP TYPE	LED
COLOR TEMPERATURE	Cool white
LAMP LENGTH	2 ft
LUMENS	4000
LUMENS PER WATT	132
OPTICAL DISTRIBUTION	Wide
MOUNTING METHOD	Flush ceiling
VOLTAGE RATING	120-277 Vac, 127/250 Vdc
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Polycarbonate
ENTRY SIZE	3/4"
FINISH	Natural aluminum
MATERIAL	Copper-free aluminum
WATTAGE	30W
POWER FACTOR	> 0.92
SPECIAL FEATURES	Integral emergency battery back-up

	IF 1946 - MLLA-M2 Linear LED with Emergency Battery Back-up
00000	IF 1939 - Champ Linear MLLA M2 LED Light Engine Fixtures
	IF 1932 - Champ Linear MLLA M2 LED Fixtures
00000000	Eaton Specification Sheet - MLLA2-UNV1-S903-EM1-M2
	Champ MLLA LED Linear
0000	Crouse-Hinds series Champ MLLA LED Linear brochure
	Crouse-Hinds series Global LED lighting portfolio
0000	Crouse-Hinds series Champ MLLA LED Linear catalog page
	Champ MLLA Hazardous Area Linear LED Light Fixtures UL certification
	Champ MLLA Hazardous Area Linear LED Light Fixtures Canadian certification
0000	Champ MLLA and Pauluhn DLLA Linear LED and Champ VMVL Intelligent LED Fixtures UL certification (Marine)
	Champ MLLA Hazardous Area Linear LED Light Fixtures UL certification (MLLA4 with Battery Back-up)

