



□□□□

Eaton MLLA2-UNV34-S891-M2

Eaton Crouse-Hinds series Champ MLLA linear LED light fixture, Cool white, 3/4" entries, Natural aluminum finish, 2 ft, Diffused glass lens, 4000 lumens, 132 lm/W, Copper-free aluminum, Flush ceiling mount, Wide, >0.95 PF, 347-480 Vac, 30W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ MLLA linear LED light fixture
CATALOG NUMBER	MLLA2-UNV34-S891-M2
UPC	662276995437
PRODUCT LENGTH/DEPTH	25.94 in
PRODUCT HEIGHT	4.42 in
PRODUCT WIDTH	7.13 in
PRODUCT WEIGHT	15.1 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
----------------------------	--------------------------------

STANDARDS TYPE	NEC/CEC
-----------------------	---------

NEC HAZARDOUS RATING	Class I, Zone 2 Class I, Division 2 Class II, Division 1 Class III
-----------------------------	---

NEMA RATING	4X
--------------------	----

INGRESS PROTECTION (IP) RATINGS	IP66 IP67
--	--------------

Product specifications

LAMP TYPE	LED
------------------	-----

COLOR TEMPERATURE	Cool white
--------------------------	------------

LAMP LENGTH	2 ft
--------------------	------

LUMENS	4000
---------------	------

LUMENS PER WATT	132
------------------------	-----

OPTICAL DISTRIBUTION	Wide
-----------------------------	------

MOUNTING METHOD	Flush ceiling
------------------------	---------------

VOLTAGE RATING	347-480 Vac
-----------------------	-------------

FREQUENCY RATING	50/60 Hz
-------------------------	----------

LENS MATERIAL	Diffused glass
----------------------	----------------

ENTRY SIZE	3/4"
-------------------	------

FINISH	Natural aluminum
---------------	------------------

MATERIAL	Copper-free aluminum
-----------------	----------------------

WATTAGE	30W
----------------	-----

POWER FACTOR	> 0.95
---------------------	--------

