



□□□□□

Eaton MLLA4-UNV34-M2

Eaton Crouse-Hinds series Champ MLLA linear LED light fixture, Cool white, 3/4" entries, Natural aluminum finish, 4 ft, Glass lens, 8000 lumens, 135 lm/W, Copper-free aluminum, Flush ceiling mount, Wide, >0.98 PF, 347-480 Vac, 59W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ MLLA linear LED light fixture
CATALOG NUMBER	MLLA4-UNV34-M2
UPC	662276997295
PRODUCT LENGTH/DEPTH	39 in
PRODUCT HEIGHT	4.42 in
PRODUCT WIDTH	7.13 in
PRODUCT WEIGHT	19.5 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66 IP67

Product specifications

LAMP TYPE	LED
COLOR TEMPERATURE	Cool white
LAMP LENGTH	4 ft
LUMENS	8000
LUMENS PER WATT	135
OPTICAL DISTRIBUTION	Wide
MOUNTING METHOD	Flush ceiling
VOLTAGE RATING	347-480 Vac
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Glass
ENTRY SIZE	3/4"
FINISH	Natural aluminum
MATERIAL	Copper-free aluminum
WATTAGE	59W
POWER FACTOR	> 0.98

0000:	
0000:	
000:	
00:	