



□□□□□

Eaton MXD01040

Eaton xDetect modular addressable fire alarm system panel, Menvier, Addressable, xDetect Control Panels, EN54 Systems, Large, Without ZI, , ,

□□□□

PRODUCT NAME	Eaton xDetect xDetect Large
CATALOG NUMBER	MXD01040
PRODUCT LENGTH/DEPTH	148 mm
PRODUCT HEIGHT	527 mm
PRODUCT WIDTH	433 mm
PRODUCT WEIGHT	10.9 kg
COMPLIANCES	EN

MOUNTING METHOD	Surface mounting
OPERATING VOLTAGE	24 VDC
NUMBER OF BATTERIES	2
BATTERY VOLTAGE	12 V
BATTERY CAPACITY	12 Ah
CLASS CHANGE CAPABILITY	Yes
CONSTRUCTION MATERIAL BACK ENCLOSURE	Mild steel
CONSTRUCTION MATERIAL FRONT ENCLOSURE	Mild steel
HUMIDITY (NON CONDENSING) - MAX	95 %
HUMIDITY (NON CONDENSING) - MIN	0 %
MAIN INPUT SUPPLY	230 Vac, 50 Hz
OPERATING TEMPERATURE - MAX	50 °C
OPERATING TEMPERATURE - MIN	-5 °C
SYSTEM TOPOLOGY	Addressable
MAXIMUM NETWORK SIZE (NUMBER OF NODES)	250
TYPE OF DISPLAY	Touchscreen
AUXILIARY FREE OUTPUT	Yes
AUXILIARY RELAYS	Fire/Fault
PRODUCT BRANDING	Eaton Menvier
SUITABLE FOR	Bus Connection
INTEGRATED FUNCTION	Addressable Interface External
EN CERTIFICATION STANDARDS	EN54-2:1997+A1:2006, EN54-4:1997+A1:2002+A2:2006
UL CERTIFICATION STANDARDS	Not Applicable
EXTERNAL CONNECTION PORTS	USB Mini-B 5 Pin

