



Eaton N001-005-OR

Cat5e 350 MHz Snagless Molded (UTP)
Ethernet Cable (RJ45 M/M) - Orange, 5 ft.
(1.52 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N001-005-OR
UPC	037332202611
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.12 lb
COMPLIANCES	RoHS REACH
CERTIFICATIONS	UL Listed cUL Listed

SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Orange
PACKAGE CONTENTS	N001-005-OR Cat5e 350 MHz Snagless Molded UTP Patch Cable (RJ45 M/M), Orange, 5 ft.
SYSTEM REQUIREMENTS	Cat5/5e For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.
IEEE STANDARDS SUPPORTED	802.3at 802.3ab
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	PoE Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Premium cabling for Cat5/5e applications Rated for 350 MHz/1 Gbps communications 26 AWG 4-pair stranded UTP with PVC jacket Snagless RJ45 male connectors Lifetime limited warranty (Worldwide) Color-coded orange for easy identification
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat5/5e
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 104°F (-10° to 40°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 122°F (-15° to 50°C)
CONDUCTOR GAUGE	26 AWG
AWG-SIZE	26AWG
CABLE LENGTH	5 Foot

OUTER CABLE DIAMETER	5.0 mm
WIRE SIZE (AWG) - MAX	26
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	14° to 104°F (-10° to 40°C)
BANDWIDTH PER TIA STANDARD	100 MHz
MAXIMUM BANDWIDTH AS TESTED	350 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	5 - 8ft (1 - 2M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Standard
CABLE STYLE	Snagless Molded



 Eaton House
30 Pembroke Road
Dublin 4, Eaton.com

