



Eaton N001-012-GY

Cat5e 350 MHz Snagless Molded (UTP)
Ethernet Cable (RJ45 M/M) - Gray, 12 ft. (3.66
m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N001-012-GY
UPC	037332172587
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.26 lb
COMPLIANCES	RoHS REACH
CERTIFICATIONS	cUL Listed UL Listed

□□□□	
SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Gray
PACKAGE CONTENTS	12Ft Gray Snagless Cat5e Patch Cable
SYSTEM REQUIREMENTS	Cat5/5e For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications
IEEE STANDARDS SUPPORTED	802.3ab 802.3at
CONNECTOR TYPE	Networking-copper
PRODUCT FEATURES	PoE Support
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	All cables feature boots with integral strain-relief and RJ45 (Male) connectors PVC 4-pair solid UTP Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications IEEE 802.3ab Lifetime limited warranty (Worldwide)
CONTACT PLATING	Gold
SIDEA CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR1	RJ45 (MALE)
SIDEB CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat5/5e
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 104°F (-10° to 40°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 122°F (-15° to 50°C)
CONDUCTOR GAUGE	26 AWG
AWG-SIZE	26AWG
CABLE LENGTH	12 Foot
OUTER CABLE DIAMETER	5.0 mm

□□	
----	--

WIRE SIZE (AWG) - MAX	26
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	14° to 104°F (-10° to 40°C)
BANDWIDTH PER TIA STANDARD	100 MHz
MAXIMUM BANDWIDTH AS TESTED	350 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	9 - 14ft (2 - 4M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Standard
CABLE STYLE	Molded Snagless
