



Eaton N001-025-YW

Cat5e 350 MHz Snagless Molded (UTP)
Ethernet Cable (RJ45 M/M) - Yellow, 25 ft.
(7.62 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series preterminated copper patch cables
CATALOG NUMBER	N001-025-YW
UPC	037332155092
PRODUCT LENGTH/DEPTH	0.5 in
PRODUCT HEIGHT	10 in
PRODUCT WIDTH	8 in
PRODUCT WEIGHT	0.52 lb
COMPLIANCES	REACH RoHS
CERTIFICATIONS	cUL Listed UL Listed

SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CM
CABLE JACKET COLOR	Yellow
PACKAGE CONTENTS	25-ft. (7.62 m) Yellow Snagless Cat5e Patch Cable
SYSTEM REQUIREMENTS	Cat5/5e For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications
IEEE STANDARDS SUPPORTED	802.3at 802.3ab
CONNECTOR TYPE	Networking-copper
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	IEEE 802.3ab PVC 4-pair solid UTP All cables feature boots with integral strain-relief and RJ45 (Male) connectors Lifetime limited warranty (Worldwide) Premium cabling for Category 5 and 5e applications—rated for 350 MHz/1 Gbps communications
CONTACT PLATING	Gold
SIDE A CONNECTOR1	RJ45 (MALE)
SIDE B CONNECTOR1	RJ45 (MALE)
SIDE B CONNECTOR3	RJ45 (MALE)
TECHNOLOGY	Cat5/5e
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 104°F (-10° to 40°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 122°F (-15° to 50°C)
CONDUCTOR GAUGE	26 AWG
AWG-SIZE	26AWG
CABLE LENGTH	25 Foot
OUTER CABLE DIAMETER	5.0 mm

WIRE SIZE (AWG) - MAX	26
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	14° to 104°F (-10° to 40°C)
BANDWIDTH PER TIA STANDARD	100 MHz
MAXIMUM BANDWIDTH AS TESTED	350 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	20 - 50ft (6 - 15M)
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	RJ45
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	RJ45 (male)
POE TYPE	Type 2 PoE+ (30W, IEEE 802.3at)
WIRING METHOD	EIA/TIA 568B
CABLE TYPE	Standard
CABLE STYLE	Snagless Molded



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

