




Eaton N020-01K-GY

Cat5e 350 MHz Stranded-Core (UTP) PVC Bulk Ethernet Cable - Gray, 1000 ft. (304.8 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series bulk cable
CATALOG NUMBER	N020-01K-GY
UPC	037332013057
PRODUCT LENGTH/DEPTH	9.45 in
PRODUCT HEIGHT	12.99 in
PRODUCT WIDTH	0.5 in
PRODUCT WEIGHT	24 lb
WARRANTY	Limited lifetime
COMPLIANCES	REACH RoHS IEEE Certified

□□□□	
CABLE JACKET RATING	CMR
CABLE JACKET COLOR	Gray
PACKAGE CONTENTS	1000-ft. Cat5e Gray Bulk Patch Cable Stranded PVC 24AWG 350MHz
SYSTEM REQUIREMENTS	Cat5/5e For making patch cables for Network Installations 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications.
IEEE STANDARDS SUPPORTED	802.3ab
CONNECTOR TYPE	Bare Wire Networking-copper
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	Premium cabling for Category 5 and 5e applications — rated for 350 MHz/1Gbps communications 4pr Stranded PVC CMR Jacket Lifetime limited warranty (Worldwide)
SIDEA CONNECTOR1	BARE WIRE
SIDEB CONNECTOR1	BARE WIRE
SIDEB CONNECTOR3	BARE WIRE
TECHNOLOGY	Cat5/5e
OPERATING TEMPERATURE RANGE	-4° to 167°F (-20° to 75°C)
STORAGE HUMIDITY RANGE	32° to 140°F (0° to 60°C)
STORAGE TEMPERATURE	32° to 140°F (0° to 60°C)
CONDUCTOR GAUGE	24 AWG
CABLE LENGTH	1000 Foot
OUTER CABLE DIAMETER	5.4 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 167°F (-20° to 75°C)
BANDWIDTH PER TIA STANDARD	100 MHz
MAXIMUM BANDWIDTH AS TESTED	350 MHz



CABLE SHIELDING	UTP
CABLE LENGTH RANGE	50ft and up (15M and up)
TAA COMPLIANCE	No
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	Bulk cable
CONDUCTOR MATERIAL	Stranded Copper
CONNECTOR	Bare wire
CABLE TYPE	Bulk
CABLE STYLE	Bulk



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

