



Eaton N022-01K-GY

Cat5e 350 MHz Solid Core (UTP) PVC Bulk Ethernet Cable - Gray, 1000 ft. (304.8 m), TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series bulk cable
CATALOG NUMBER	N022-01K-GY
UPC	037332013071
PRODUCT LENGTH/DEPTH	13.78 in
PRODUCT HEIGHT	10.63 in
PRODUCT WIDTH	13.78 in
PRODUCT WEIGHT	20 lb
WARRANTY	Limited lifetime
COMPLIANCES	TAA Compliant REACH RoHS IEEE Certified

□□□□	
CABLE JACKET RATING	CMR
CABLE JACKET COLOR	Gray
PACKAGE CONTENTS	1000-ft. Cat5e Gray Bulk Patch Cable Solid PVC 24AWG 350MHz
SYSTEM REQUIREMENTS	Cat5/5e For all non-Plenum horizontal premise (in-wall) wiring applications for Network Installations 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications.
IEEE STANDARDS SUPPORTED	802.3ab
CONNECTOR TYPE	Bare Wire Networking-copper
PRODUCT FEATURES	TAA Compliant
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	4pr Solid - PVC CMR Rated Jacket Lifetime limited warranty (Worldwide) Premium cabling for Category 5 and 5e applications — rated for 350 MHz/1Gbps communications
SIDEA CONNECTOR1	BARE WIRE
SIDEB CONNECTOR1	BARE WIRE
SIDEB CONNECTOR3	BARE WIRE
TECHNOLOGY	Cat5/5e
OPERATING TEMPERATURE RANGE	-4° to 167°F (-20° to 75°C)
STORAGE HUMIDITY RANGE	32° to 140°F (0° to 60°C)
STORAGE TEMPERATURE	32° to 140°F (0° to 60°C)
CONDUCTOR GAUGE	24 AWG
CABLE LENGTH	1000 Foot
OUTER CABLE DIAMETER	5.1 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	-4° to 167°F (-20° to 75°C)
BANDWIDTH PER TIA	100 MHz

STANDARD	
MAXIMUM BANDWIDTH AS TESTED	350 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	50ft and up (15M and up)
TAA COMPLIANCE	Yes
CABLE SHEATH MATERIAL	UTP
CONNECTOR GROUP	Bulk cable
CONDUCTOR MATERIAL	Solid Copper
CONNECTOR	Bare wire
CABLE TYPE	Bulk
CABLE STYLE	Bulk Solid
