



Eaton N028-01K-GY

Cat5e 350 MHz Solid Core Outdoor-Rated (UTP) PVC Bulk Ethernet Cable - Gray, 1000 ft. (304.8 m)

□□□□

PRODUCT NAME	Eaton Tripp Lite series bulk cable
CATALOG NUMBER	N028-01K-GY
UPC	037332141491
PRODUCT LENGTH/DEPTH	15 in
PRODUCT HEIGHT	9 in
PRODUCT WIDTH	14.6 in
PRODUCT WEIGHT	24.9 lb
COMPLIANCES	IEEE Certified REACH RoHS
CERTIFICATIONS	UL Listed cUL Listed



Powering Business Worldwide



SPECIAL FEATURES	0% to 90% RH, Non-Condensing
CABLE JACKET RATING	CMR CMX
CABLE JACKET COLOR	Gray
PACKAGE CONTENTS	1000ft. Box Cat5e Outdoor Rated PVC Bulk Cable
SYSTEM REQUIREMENTS	Cat5/5e
IEEE STANDARDS SUPPORTED	802.3ab 802.3at
CONNECTOR TYPE	Networking-copper Bare Wire
CABLE JACKET MATERIAL	PVC
NETWORK SPEED	1 Gbps (Gigabit)
PRODUCT HIGHLIGHTS	4PR Solid conductors for Low Attenuation Loss UV Rated jacket prevents drying and cracking CMX Outdoor rating; Temp range -40F to +140F
CONTACT PLATING	Gold
SIDEA CONNECTOR1	BARE WIRE
SIDEB CONNECTOR1	BARE WIRE
SIDEB CONNECTOR3	BARE WIRE
TECHNOLOGY	Cat5/5e
OPERATING HUMIDITY	0% to 90% RH, Non-Condensing
OPERATING TEMPERATURE RANGE	14° to 104°F (-10° to 40°C)
STORAGE HUMIDITY RANGE	0% to 90% RH, Non-Condensing
STORAGE TEMPERATURE	5° to 122°F (-15° to 50°C)
CONDUCTOR GAUGE	24 AWG
CABLE LENGTH	1000 Foot
OUTER CABLE DIAMETER	5.5 mm
NUMBER OF CONDUCTORS	4 Pair
OPERATING TEMPERATURE	14° to 104°F (-10° to 40°C)
BANDWIDTH PER TIA STANDARD	100 MHz
MAXIMUM BANDWIDTH AS TESTED	350 MHz
CABLE SHIELDING	UTP
CABLE LENGTH RANGE	50ft and up (15M and up)
CABLE SHEATH	UTP



