



Eaton N063-002

2Port DIN Rail Mounting Metal Module for a Snap-in Keystone Jack or in-line coupler

□□□□

PRODUCT NAME	Eaton Tripp Lite series mounting module
CATALOG NUMBER	N063-002
PRODUCT LENGTH/DEPTH	1.64 in
PRODUCT HEIGHT	2.12 in
PRODUCT WIDTH	1.94 in
PRODUCT WEIGHT	0.05 lb
COMPLIANCES	TAA Compliant UKCA RoHS CE Marked REACH

□□□□	
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	10% to 85% RH, (Non-Condensing)
COLOR	Silver
PANEL APPLICATIONS	Ethernet
PRODUCT FEATURES	Keystone Jacks TAA Compliant DIN Mountable
PRODUCT HIGHLIGHTS	Built-in mounting clip attaches to standard 35 mm DIN rail with no tools needed Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases Heavy-duty metal construction ideal for industrial Ethernet network applications Dual blank cutouts compatible with all keystone jacks and couplers
SIDEA CONNECTOR1	KEYSTONE JACK CUTOUT
OPERATING TEMPERATURE	-13° to 122°F (-25° to 50°C)
OPERATING TEMPERATURE RANGE	-13° to 122°F (-25° to 50°C)
STORAGE TEMPERATURE RANGE	-40° to 158°F (-40° to 70°C)
TECHNOLOGY	Cat6 Cat5/5e Cat6a
PRIMARY FORM FACTOR	DIN-Rail
MATERIAL	SUS304 & SPCC NI PLATE (METAL)
NUMBER OF PORTS	2

□□
