



Eaton N063-008-ENC

8Port DIN Rail Mounting Keystone Panel with Grounding, for a Snap-in Keystone Jack or in-line coupler

□□□□

PRODUCT NAME	Eaton Tripp Lite series patch panel
CATALOG NUMBER	N063-008-ENC
UPC	037332276933
PRODUCT LENGTH/DEPTH	3.1 in
PRODUCT HEIGHT	6.06 in
PRODUCT WIDTH	2.19 in
PRODUCT WEIGHT	0.44 lb
COMPLIANCES	UKCA REACH CE Marked RoHS TAA Compliant

□□□□	
TYPE	DIN Rail
OPERATING HUMIDITY RANGE	10% to 85% RH, Non-Condensing
STORAGE HUMIDITY RANGE	10% to 85% RH, (Non-Condensing)
COLOR	Black Silver
PANEL APPLICATIONS	Ethernet
PRODUCT FEATURES	Keystone Jacks Numbered Ports TAA Compliant DIN Mountable
PRODUCT HIGHLIGHTS	Built-in mounting clip attaches easily to standard 35 mm DIN rail with no tools needed 8 front blank cutouts compatible with all keystone jacks and couplers Rugged metal front construction with plastic rear frame for industrial applications Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases Numbered ports allow at-a-glance identification of cable connections
SIDE A CONNECTOR1	KEYSTONE JACK CUTOUT
OPERATING TEMPERATURE	-13° to 122°F (-25° to 50°C)
OPERATING TEMPERATURE RANGE	-13° to 122°F (-25° to 50°C)
STORAGE TEMPERATURE RANGE	-40° to 158°F (-40° to 70°C)
TECHNOLOGY	Cat5/5e Cat6 Cat6a
PRIMARY FORM FACTOR	DIN-Rail
MATERIAL	Plastic (PC FR) & Metal (SPCC/FE)
NUMBER OF PORTS	8

□□	
----	--

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

