



Eaton N201-003-GY

Cat6 Gigabit Snagless Molded (UTP) Ethernet Cable (RJ45 M/M), Gray, 3 ft. (0.91 m)



| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Tripp Lite series preterminated copper patch cables |
| CATALOG NUMBER | N201-003-GY |
| UPC | 037332099822 |
| PRODUCT LENGTH/DEPTH | 0.5 in |
| PRODUCT HEIGHT | 9 in |
| PRODUCT WIDTH | 7 in |
| PRODUCT WEIGHT | 0.09 lb |
| COMPLIANCES | RoHS REACH IEEE Certified |
| CERTIFICATIONS | UL Listed cUL Listed |



Powering Business Worldwide



| | |
|------------------------------------|--|
| SPECIAL FEATURES | 0% to 90% RH, Non-Condensing |
| CABLE JACKET RATING | CM |
| CABLE JACKET COLOR | Gray |
| PACKAGE CONTENTS | 3-ft. Cat6 Gray Gigabit Patch Cord Snagless Molded |
| SYSTEM REQUIREMENTS | PoE Cat6 For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring TYPE 3 applications as well as EIA/TIA applications. |
| IEEE STANDARDS SUPPORTED | 802.3an 802.3at |
| CONNECTOR TYPE | Networking-copper |
| PRODUCT FEATURES | Snagless Connector PoE Support |
| CABLE JACKET MATERIAL | PVC |
| NETWORK SPEED | 1 Gbps (Gigabit) |
| PRODUCT HIGHLIGHTS | Designed to meet Category 6 specifications; reduces cross-talk and return loss IEEE 802.3ab PVC 4-pair stranded UTP Premium cabling for Category 6, Category 5e and Category 5 applications—rated for 550 MHz/1 Gbps communications All cables feature boots with integral strain-relief and RJ45 (Male) connectors |
| CONTACT PLATING | Gold |
| SIDEA CONNECTOR1 | RJ45 (MALE) |
| SIDEB CONNECTOR1 | RJ45 (MALE) |
| SIDEB CONNECTOR3 | RJ45 (MALE) |
| TECHNOLOGY | Cat6 |
| OPERATING HUMIDITY | 0% to 90% RH, Non-Condensing |
| OPERATING TEMPERATURE RANGE | 14° to 122°F (-10° to 50°C) |
| STORAGE HUMIDITY | 0% to 90% RH, Non- |

